



**TYPE A
AKLOPT**



>> Use (*)

Thanks to its technical features, this glove is particularly suitable for all major heavy works requiring good protection to abrasion and tear.

Shellfish farming, fish trade, industrial fishing, deep sea fishing, handling construction materials, masonry ...


This glove also provides protection against some chemicals and may be used for cleaning, maintenance...

>> Technical features

- ✓ **Construction / material:** Cut and sewn liner. 100% cotton interlock. Fully latex(*) dipped. Smooth finish
- ✓ **With Actifresh®.**
- ✓ **Color:** blue.
- ✓ **Length:** 300 mm. (average value).
- ✓ **Sizes:** 6 1/2, 7 1/2, 8 1/2, 9 1/2, 10 1/2.
- ✓ **Packing:** - carton of 100 pairs.
- bundle of 10 pairs.



Learn more: www.singer.fr



>> Advantages

- ✓ Good insulation and good comfort thanks to the interlock liner.
- ✓ The guarantee and benefits of an ISO9001 certified manufacturing: quality of products, regularity....
- ✓ Anti-bacterial effect of the Actifresh® treatment deprives bacteria from developing and growing.
- ✓ The Actifresh® treatment is effective against bacteria, fungi, rust, stains and algae in preventing these micro-organisms from developing.
- ✓ It promotes a longer life and avoids the creation of bad odours.
- ✓ Cotton liner: brings the comfort of a natural material which facilitates the absorption of perspiration.

>> Conformity

This glove has been tested according to the following European standards:

- **EN420 : 2003 +A1 : 2009.** Protective gloves - General requirements and test methods.
- **EN388 : 2016.** Protective gloves against mechanical risks.
- **EN ISO 374-1 : 2016.** Protective gloves against dangerous chemicals and micro-organisms.
Part 1: Terminology and performance requirements for chemical risks.
- **EN 374-2 : 2014.** Protective gloves against dangerous chemicals and micro-organisms.
Part 2: Determination of resistance to penetration.
- **EN 16523-1 : 2015.** Determination of material resistance to permeation by chemicals.
Part 1: Permeation by liquid chemical under conditions of continuous contact.
- **EN 374-4 : 2013.** Protective gloves against chemicals and micro-organisms.
Part 4: Determination of resistance to degradation by chemicals.
- **EN ISO 374-5: 2016.** Protective gloves against dangerous chemicals and micro-organisms.
Part 5: Terminology and performance requirements for micro-organisms risks.
- **EN 407 : 2004.** Protective gloves against thermal risks (heat and/or fire)

It complies with **European Regulation (EU) 2016/425** on Personal Protective Equipment (PPE). **Category III.**

EU type examination certificate (**module B**) issued by **SATRA (Ireland)**, notified body **n°2777**.

The PPE is subject to the conformity assessment procedure based on quality assurance of the production process (**Module D**) set out in Annex VIII (Category III) under surveillance of **SGS**, notified body **n°0120**.



Your **SINGER® SAFETY** partner




(*) Type of use is given as a guide only. It is to the end user to check whether the product is suitable or not for the intended use. Before any use, read carefully the instructions enclosed with the product. Issue LS 2018_09_10. Warning: people allergic to latex should avoid contact with this material. Copyright: Singer, Foalra

EN 388: 2016. Protective gloves against mechanical risks

Mechanical data. Information about levels.	Level 1	Level 2	Level 3	Niveau 4	Level 5	Levels ▼
Abrasion resistance (number of cycles)	100	500	2000	8000	-	3
Blade cut resistance (index)	1,2	2,5	5,0	10,0	20,0	1
Tear resistance (in Newtons)	10	25	50	75	-	3
Perforation resistance (in Newtons)	20	60	100	150	-	1

Cut resistance (as per EN ISO13997) (TDM test)	Level A	Level B	Level C	Level D	Level E	Level F	Level
	2	5	10	15	22	30	A

EN 388 : 2016






3 1 3 1 A

EN ISO 374-1: 2016 / TYPE A.

Protective gloves against dangerous chemicals and micro-organisms.
Part 1. Terminology and performance requirements for chemical risks.

EN ISO 374-5 : 2016.

Protective gloves against dangerous chemicals and micro-organisms.
Terminology and performance requirements for micro-organisms risks.

EN ISO 374-1 : 2016 / TYPE A	EN ISO 374-5 : 2016		Chemicals ▼	Code ▼	Class ▼	Type A gloves are gloves that have passed i) penetration test as per EN 374-2:2014 (water leak & air leak test) ii) achieved at least Level 2 (more than 30 min) breakthrough time for chemical permeation test as per EN 16523-1:2015 against minimum 6 chemicals from the list of 18 test chemicals on Table 2 of EN ISO 374-1:2016. The 3 tested chemicals are represented by their code letter and marked under the pictogram and iii) have performed chemical degradation test as per EN 374-4:2013 for each chemical claimed and the results are as reported here.
			Methanol	A	3	
			Sodium hydroxyde 40 %	K	6	
			Sulphuric acid 96%	L	4	
			Ammonium hydroxide 25 %	O	3	
			Hydrogen peroxide 30%	P	6	
			Formaldehyde 37%	T	6	

EN 374-4: 2013.

Protective gloves against chemicals and micro-organisms.
Part 4. Determination of resistance to degradation by chemicals.

Chemicals ▼	Code ▼	Mean Degradation ▼	Appearance of the sample after testing
Methanol	A	12.2%	Shrunken
Sodium hydroxyde 40 %	K	-10.1%	Shrunken
Sulphuric acid 96%	L	47.1%	Shrunken, discolored and flaky
Ammonium hydroxide 25%	O	-13.9%	Shrunken
Hydrogen peroxide 30%	P	-14.8%	Slightly Shrunken
Formaldehyde 37%	T	-9.0%	Shrunken


Protection against bacteria & fungi: PASS
Protection against Viruses: Not tested

EN ISO 374-1: 2016 Chemical Permeation Performance levels	
Measured breakthrough time (min)	Permeation performance level
> 10 min	Class 1
> 30 min	Class 2
> 60 min	Class 3
> 120 min	Class 4
> 240 min	Class 5
> 480 min	Class 6

Your **SINGER® SAFETY** partner



EN 407 : 2004. Protective gloves against thermal risks (heat and/or fire)

EN 407: 2004		Thermal data (tests)	Performance levels chart				Results ▼
			1	2	3	4	
 <p>X 2 X X X X</p> <p>The performance levels are only for the complete glove, all layers included. «X means that the glove has not been submitted to the test.</p>	a1	Burning behaviour	≤ 20s	≤ 10s	≤ 3s	≤ 2s	X
	a2		No requirement	≤ 120s	≤ 25s	≤ 5s	
	b	Contact heat	100°C ≥ 15 s	250°C ≥ 15 s	350°C ≥ 15 s	500°C ≥ 15 s	2
	c	Convective heat	≥ 4 s	≥ 7 s	≥ 10 s	≥ 18 s	X
	d	Radiant heat	≥ 7 s	≥ 20 s	≥ 50 s	≥ 95 s	X
	e	Small splashes of molten metal	≥ 10 s	≥ 15 s	≥ 25 s	≥ 35 s	X
	f	Large splashes of molten metal	30g	60g	120g	200g	X

- a1) After flame time (seconds).
- a2) After glow time (seconds).
- b) Contact temperature/ Threshold time (seconds).
- c) Heat transfer index (HTI) (seconds).
- d) Heat transfer (T₂₄) (seconds).
- e) Number of droplets which produce a temperature rise of 40 °C.
- f) Molten iron (in grams).

Your SINGER® SAFETY' partner

